

Product certificate
K90330/01

Issued 2015-12-15

Replaces

Page 1 of 3

Close coupled suites

STATEMENT BY KIWA

With this product certificate, issued in accordance with the Kiwa Regulations for Product Certification, Kiwa declares that legitimate confidence exists that the products supplied by


HSIL Limited

as specified in this product certificate and marked with the Kiwa®-mark in the manner as indicated in this product certificate may, on delivery, be relied upon to comply with

Kiwa evaluation guideline BRL-KK621/06 “Close coupled suites” dated 01-02-2012

which covers the requirements of

EN 997: 2003 “WC-pans and WC-suites with integral trap”.



Bouke Meekma
Kiwa

Publication of the certificate is allowed.

Advice: consult www.kiwa.nl in order to ensure that this certificate is still valid.

Kiwa Nederland B.V.

Sir Winston Churchillaan 273
Postbus 70
2280 AB RIJSWIJK
The Netherlands

Tel. +31 88 998 44 00
Fax +31 88 998 44 20
info@kiwa.nl
www.kiwa.nl



288/150609

Supplier

HSIL Limited
301-302, III Floor, Park Centra,
Sector 30NH-8
Gurgaon, Haryana - 122 001
India

Tel. +91 127 62 30 485
Fax +91 127 62 34 428
www.hindwarehomes.com

Certification process consists of initial and regular assessment of:

- quality system
- product

Close coupled suites

Technical specification

Unless otherwise mentioned the products specified are classified as Class 1 products.

The products mentioned below belong to this certificate.

Close coupled suites with nominal flush of 6 litres

Model Cleo

Wash down WC-pan no. 20050; vertical concealed outlet (220 mm); with flushing cistern no. 21033 incorporating the following configuration:

- Geberit bottom inlet valve type Impuls TYP360; with brass inlet connection
- Dual flush mechanism 6/3 Compas C211

Product will be delivered with all installation means; matching outlet spigot connections to comply with EN33 and with corresponding matching lavatory seat.

Model Florence

Wash down WC-pan no. 92058; vertical concealed outlet (220 mm); with flushing cistern no. 92122, incorporating the following configuration:

- Geberit bottom inlet valve type Impuls TYP360; with brass inlet connection
- Dual flush mechanism 6/3 Compas C211

Product will be delivered with all installation means; matching outlet spigot connections to comply with EN33 and with corresponding matching lavatory seat.

Above mentioned products are also in compliance with the European Standard EN997: 2012 +A1.

Close coupled suites

Application and use

Close coupled suites are designed as flushing devices to be connected to drinking water installations with a maximum water temperature of 30 °C.

Marking

The WC pan, cistern and float operated valve of the close coupled suites are marked with the word mark "KIWA". Example:

On the WC-pan this word mark shall be followed by the number 6, indicating the flushing volume.

Close coupled suite marked as follows:

WC-pan: "KIWA-6"

Cistern: "KIWA"

Float valve: "KIWA"

Place of the mark:

- on the WC-pans between the attachment holes of the lavatory seat or on the sides;
- on the float valves on the body;
- on the cisterns on the left side, right side or front or on the inside above water level.

By this marking it is given that the close coupled suite is Kiwa certified and intended for use with a full flush of 6 litres. This flushing volume is indicated by the highest waterline in the cistern.

Compulsory specifications:

name or mark of the manufacturer:

- on the WC-pans between the attachment holes of the lavatory seat or on the sides;
- on the float valves on the body;
- on the cisterns on the left side, right side or front or on the inside above water level;
- additional markings as specified in EN 997 on a removable label.

Method of marking:

- indelible;
- visible after assembly.

RECOMMENDATIONS FOR CUSTOMERS

Check at the time of delivery whether:

- the supplier has delivered in accordance with the agreement;
- the mark and the marking method are correct;
- the products show no visible defects as a result of transport etc.

If you should reject a product on the basis of the above, please contact:

- HSIL Limited
- and, if necessary,
- Kiwa Nederland B.V.

Consult the supplier's processing guidelines for the proper storage and transport methods.